

# **GL030–0223** BOWMAN<sup>®</sup> *Signature Series* – Glove Box Dispenser – Triple



## **Related Products (each sold separately):**

 GL030-0233 : BOWMAN<sup>®</sup> Signature Series - Glove Box Dispenser -Cherry Fauxwood ABS plastic - Triple with Dividers (shown below)

## **Product Description:**

- Glove Box Dispenser Triple with Dividers
- Holds three boxes of gloves
- Three-way keyholes for vertical or horizontal wall mounting
- BOWMAN® Signature Series Maple Fauxwood ABS Plastic

## Primary Area for Product Usage:

Anywhere gloves are needed

### Dispenses:

- Box(es) no larger than 5.50"W x 10.00"H x 3.75"D (14.0 cm x 25.4 cm x 9.5 cm)
- Box(es) no smaller than 4.50"W x 9.00"H x 3.00"D (11.4 cm x 22.9 cm x 7.6 cm)


## Package Specifications:

- Package Quantity: 4 per case
- 18"L x 16"W x 10"H (45.7 cm x 40.6 cm x 25.4 cm)
- 8.0 lbs (3.6 kg) approximated

**Product Specifications** (overall external dimensions):

- 17.00"W x 10.13"H x 4.00"D (43.2 cm x 25.7 cm x 10.2 cm)
- 1.4 lbs (0.6 kg) approximated

Mounting Specifications:








## Installation

Always mount dispensers securely prior to loading with product.



 Mount securely to a wall with screws approved and supplied by building maintenance.

## Parts included:

Dispenser

## Tools <u>Required:</u>

No tools required to assemble dispenser

**Care and Construction** Fauxwood ABS Plastic

## Material Characteristics

**Designed for Long-Term, Heavy-Duty** Applications

The combination of copolymers (Acrylonitrile, Butadiene, and Styrene) gives ABS an excellent combination of strength, rigidity, and toughness. The fauxwood finish is ARVINYL laminate created from a semi-rigid film.

ABS is chemical and stress-crack resistant. It is tough, dimensionally stable, and will hold up to long-term use. To ensure product longevity, fauxwood products should not be mounted in very hot or cold areas.

Use mild soap and water to clean. Petroleum-based oils, solvents, and paints should not be used.

Standard hospital cleaning supplies are approved for use on our ABS plastic products.

GL030-0223- Installation/Characteristics & Care

Information subject to change without notice. Dimensions are approximate. (Not to scale)

20325 71<sup>st</sup> Ave NE, Suite D, Arlington, WA 98223 800.962.4660 • www.BowmanDispensers.com ©2019 BOWMAN® Manufacturing Company, Inc. All Rights Reserved. Product specifications subject to change without notification. Consumables not included. GL0300223TDSa