

\_\_\_\_\_

20 e- rms

CAMERA CONTROLS

Read Noise

Integration Time1/1000 to 3 sec.ShutterRolling shutter with single frame captureROIUser SelectableAuto ExposureAutomatic / ManualWhite BalanceAutomatic / ManualGainProgrammable / 1 to 10X optimizableInterface ConnectorUSB 2.0 high speed interfaceDimensions (L x W x H)3.85 x 2.00 x 2.75 inches

Mass300gPower RequirementUSB 2.0 bus power, or external 5VDC - 500mAPower Consumption~2.5WattsPrintOperating Temperature0° C to +50° COperating Humidity5%-95%, Non-condensing

**Downloadable Documents** 

Thinity Caputre & Analyze

Model: 26100-215 Shipping Weight: 1.5lbs

Add to Cart:	1
	-

Add to Cart

Copyright © 2008 Aven, Inc. 4595 Platt Road Ann Arbor, MI 48104 734-973-0099 sa