ArtNumber: 701097				
(\$ 24,5 ° 0) (\$ 24,5 - 0,3)	35 ±0,3		(0,4 ±0,1) (0,7 ±0,1)	1 of the devices for the mass production definitely
- Samples can deviate in the execution from the serie.	,3 ±0,05 ) (+) (+) (+) (+) (+) (+) (+) (+	5,08 ±0,3		- Dimensions and tolerances can be specified only after the testing of th
All framed values will be used for dimension checking !				
The Products of Renata SA are neither designed nor authorized for use in certain areas of appliction of environment. For further details we refer to our webpage: <u>www.renata.com/downloads/restriction_of_use</u>				
Rev. (1) 13.09.2019 SRi	Rev. <sub>O</sub>		Customer's Approva	
Rev. <sub>O</sub> .	Rev. <u></u>		Date	
Rev. <sub>O</sub> .	Rev. <sub>O</sub>		Signature	
Titel:		Scale	Drawn 05.01.0	5 SRi
CR2450NRH	1_1 F	2:1	Checked 13.09.19	HSn
	· <b>_</b> ·		Approved 16.09.19	MDi
renata batteries	CH-4452 Itinger Switzerland	<sup>۱</sup> 3.	8735.4-	1