

599 Menlo Drive, Suite 100 Rocklin, California 95765, USA **Office:** (916) 624-8333 **Fax:** (916) 624-8003 General: info@parallaxinc.com Technical: support@parallax.com Web Site: www.parallax.com Educational: http://www.parallax.com/html\_pages/edu/

# Standard Mini Servo (#900-00010)

### **General Information**

The Parallax Mini standard servo is ideal for small robotics and basic movement projects. These servos will allow a movement range of 0 to 180 degrees.



## **Technical Specifications**

> Power 4.8vdc to 6vdc max

> Speed 0 deg to 180 deg in .5 seconds on average

> Weight 26.6 grams/.94oz

> Torque 2.8 kg-cm/39oz-in

> Size mm (L x W x H)
40.5x20.0x38.0

> Size in (L x W x H) 1.38x.67x1.26



Measurements are in mm

## Wiring setup



The servo is controlled by pulsing of its signal line. If you are using a Basic Stamp this is done with the pulsout command. Below is stamp code that will help you with basic control of a servo. The codes below may not move the servos from on extreme to another but is will give you a general demonstration on function.

#### 'Stamp1

```
symbol temp = w0
start:
    for temp = 70 to 250 step - 1
    pulsout 0,temp
    pause 50
    next
    for temp = 250 to 70
    pulsout 0,temp
    pause 50
    next
goto start
```

### 'Stamp 2 ,2e,2pe

temp VAR Word
start:
 FOR temp = 1200 TO 305
 PULSOUT 0,temp
 PAUSE 20
 NEXT
 FOR temp = 305 TO 1200
 PULSOUT 0,temp
 PAUSE 20
 NEXT
GOTO start

### 'Stamp 2sx,2p24/40

temp var word
start:
 for temp = 500 to 3000
 pulsout 0,temp
 pause 50
 next
 for temp = 3000 to 500
 pulsout 0,temp
 pause 50
 next

goto start